


# Ampule Sealer (S type)

It is easy to seal by setting up the Ampule on the holder, transferring it to Sealer position and picking up its tip with tweezers. Revolution of Ampule is done by roller, so it seals evenly, and it can be done well even for the first time user with limited experience. It is unnecessary to lay a pipe for the air since small sized compressor is already built in.



## SPECS

Targeted Ampule : 1mL ~ 20mL

Sealing capacity : more than 100bottles / hr

Sealing Gas : City gas or LPG

Power Supply : 100V

Machine Size : W172 x D208 x H240mm



**ASAHI SEIKI Co.,LTD.**

URL : <http://www.asahiseiki.jp> E-mail : [info@asahiseiki.jp](mailto:info@asahiseiki.jp)

Head office & Factory

382-25 Sonnou-chou Inage-ku Chiba 263-0051 Japan

Phone: (81) 43 284 6690 Fax: (81) 43 310 3391